




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
BEAM DIVERGENCE (mrad)	3.5
COLOR	Infrared
OUTPUT POWER (mW)	50
POINT STABILITY AFTER WARM UP (mrad/°C)	<0.05
POLARIZATION	>10:1
POWER STABILITY (%)	<2% RMS over 4 hours
WAVELENGTH (nm)	980
MODULATION FREQUENCY (kHz)	1
BEAM DIAMETER (mm)	3.5

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®



ALL DIMS IN

mm

TITLE

Laser LC Turnkey 980nm x 50mW

DWG NO

19490

SHEET
1 OF 1