




NOTES:

- 1. SUBSTRATE: POLYMER FILM XP42-100
- 2. OPERATING TEMPERATURE (°C): -10 to +60
- 3. OPERATING HUMIDITY (%): ≤80 (No Condensation)
- 4. WAVELENGTH RANGE: 400-700nm
- 5. POLARIZATION: >99.98
- 6. TRANSMISSION (%):  
SINGLE 42 ±2  
PARALLEL: 36.4  
CROSSED: <0.004
- 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	50mm Dia. Linear Polarizer (XP42-100)	
ALL DIMS IN	mm	DWG NO	19953	SHEET 1 OF 1