

NOTES:

1. SUBSTRATE:  
NITROCELLULOSE

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE


8% R @ 400 - 2200nm @ 45° AOI

92% T @ 400 - 2200nm @ 45° AOI



R/T TOLERANCE: ±3%

S2: NONE

3. ROHS COMPLIANT



SECTION A-A



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø 203.2	Ø 203.2
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

TITLE

203.2mm Clear Aperture 8R/92T, Pellicle  
Beamsplitter

DWG NO

22589

SHEET  
1 OF 1