



NOTES:

1. SUBSTRATE
GORILLA® GLASS
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: ¼ WAVE MgF2 @ 550nm
R(AVG) < 1.75% FROM 400 - 700nm
3. FINE GRIND SURFACE
4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	22.50	22.50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

		Edmund Optics®	
		TITLE 25mm Diameter, MgF2 Coated, Gorilla Glass® Window	
ALL DIMS IN mm	DWG NO 22852	SHEET 1 OF 1	