




NOTES:


- 1. SUBSTRATE:
CP42HE Laminated Between Glass
- 2. OPERATING TEMPERATURE: -40 to +80 °C
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: Uncoated
- 4. EFFICIENCY OF LINEAR COMPONENT: >99.90 %
- 5. WAVELENGTH RANGE: 400 - 700 nm
- 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	15mm Dia. Left-Handed Uncoated Glass Circular Polarizer (CP42HE)	
ALL DIMS IN	mm	DWG NO	19927	SHEET 1 OF 1