NOTES:

1. SUBSTRATE: SAPPHIRE (AL2O3) DO NOT MANUFACTURE PARTS TO THIS DRAWING


- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(ABS) ≤1.5% @ 750 - 800nm R(ABS) ≤1.0% @ 800 - 1550nm R(AVG)avg ≤0.7% @ 750 - 1550nm



FINE GRIND SURFACE

5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
CLEAR APERTURE	Ø11.43	Ø11.43		
SURFACE FLATNESS	2λ	2λ		
SURFACE QUALITY	80-50	80-50		
BIREFRINGENCE (n _o -n _e)	0.008	0.008		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

_			Edmund Optics®			
THIRD ANGLE TITLE		TITLE	12.7mm Dia., 2mm Thick, NIR II AR Coated Sapphire Window			
	ALL DIMS IN	mm	DWG NO	20927	SHEET 1 OF 1	