


NOTES:

- 1. SUBSTRATE: IR GRADE FUSED SILICA
- 2. COATING:  
  
S1 & S2: R(AVG) ≤ 0.5% FROM 350-700nm @ 0° AOI
- 3. CENTERING: < 3 ARCMIN
- 4. RoHS: COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	Ø22.86	Ø22.86
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN      mm

**EO**® **Edmund Optics®**

TITLE	25.4mm Diameter x 250mm FL, 350-700nm, Ultrafast Thin PCX Lens		
DWG NO	22642		SHEET 10 OF 19