




FOCAL LENGTH (EFL): $-6 \pm 0,06$

BACK FOCAL LENGTH (BFL): $-6,56$

1 AR COATING: YAG-BBAR

R(abs) $< 0.25\%$ @ 532nm

R(abs) $< 0.25\%$ @ 1064nm

R(avg) $< 1.0\%$ @ 500 - 1100nm

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 4,71 $\pm$ 0,005 CV	GLASS N-SF11 785/258	R ∞ PL
Øe 2,5		Øe 2,5
3/ 3 (0,5) $\lambda=632,8$ nm		3/ 3 (0,5) $\lambda=632,8$ nm
4/ -		4/ 3,82'
5/ 20 - 10 (MIL-PRF-13830B)		5/ 20 - 10 (MIL-PRF-13830B)
6/ -		6/ -


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



ALL DIMS
IN:

mm



Edmund Optics®

TITLE

LENS PCV 3 X -6 YAGBBAR TS

DWG NO

21299

SHEET SIZE
A4

SHEET
1 OF 1

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110