

NOTES:

1. SUBSTRATE: N-BK7
2. COATING
S1 & S2: NIR+
Ravg <0.5% @ 600 - 1050nm @ ±30° AOI
Rabs <1.5% @ 600 - 1050nm @ ±30° AOI

3. EDGES: FINE GRIND SURFACE

4. CENTERING: < 3 ARCMIN



5. ASPHERIC FIGURE ERROR: 0.016 µm RMS

6. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z(Y) = \frac{\left(\frac{1}{\text{RADIUS}}\right) * Y^2}{1 + \sqrt{1 - (1+k) * \left(\frac{1}{\text{RADIUS}}\right)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14} + M * Y^{16}$$

7. ROHS: COMPLIANT


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



COEFFICIENT TABLE 6.

	S1
SEMI-DIAMETER	1.250000E+01
COEFFICIENT	
(1/RADIUS)	5.159959E-02
k	-6.698934E-01
D	0.000000E+00
E	1.876737E-06
F	8.930244E-10
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00
M	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL: 37.50mm	 Edmund Optics ®		
SHAPE	CONVEX	PLANO	BFL: 31.09mm			
RADIUS	19.380	INFINITY	THIRD ANGLE PROJECTION 	TITLE	25mm Dia x 37.5mm FL, NIR+, High Precision Aspheric Lens	
SURFACE QUALITY	40 - 20	40 - 20				
CLEAR APERTURE	Ø22.50	Ø22.50				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	22906
					SHEET 1 OF 1	