




FOCAL LENGTH (EFL): $-12 \pm 0,12$
 BACK FOCAL LENGTH (BFL): $-13,26$

1 AR COATING: YAG-BBAR
 R(abs) $< 0.25\%$ @ 532nm
 R(abs) $< 0.25\%$ @ 1064nm
 R(avg) $< 1.0\%$ @ 500 - 1100nm

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 9,42±0,009 CV Øe 8,1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF11 785/258	R ∞ PL Øe 8,1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ 1,27' 5/ 40 - 20 (MIL-PRF-13830B) 6/ -


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



ALL DIMS
IN:

mm



Edmund Optics®

TITLE

LENS PCV 9 X -12 YAGBBAR TS

DWG NO

21307

SHEET SIZE
A4

SHEET
1 OF 1

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110