



NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: VIS 0° (425-675nm)  
S2: VIS 0° (425-675nm)  
Ravg ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE

- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                 | S1                  | S2                  |
|-----------------|---------------------|---------------------|
| SHAPE           | PLANO               | PLANO               |
| SURFACE QUALITY | 60-40               | 60-40               |
| CLEAR APERTURE  | 45.00 x 45.00       | 45.00 x 45.00       |
| BEVEL           | PROTECTED AS NEEDED | PROTECTED AS NEEDED |



ALL DIMS IN mm

**Edmund Optics®**

TITLE

50mm Sq., 1mm Thick, VIS 0° Coated λ/4 N-BK7 Window

DWG NO

23396

SHEET  
14 OF 48