



NOTES:

1. SUBSTRATE:
N-BK7
2. S2 TO BE PARALLEL TO S1 TO <30 ARCSEC
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2: Ravg ≤0.5% @ 600 - 1050nm

△ 4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
WAVELENGTH RANGE	600-1050nm	600-1050nm
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE

30mm Diameter NIR I Coated, Ultra-Thin
N-BK7 Window

DWG NO

22049

SHEET
6 OF 8