


NOTES:

1. SUBSTRATE:  
Fused Silica (or equivalent)
2. CENTERING TOLERANCE (AT 587.6nm): <1 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1 & S2: NONE
4. FINE GRIND SURFACE (ADD INK NOTE AS NEEDED)
5. FOCAL LENGTH (EFL): 40mm  
BACK FOCAL LENGTH (BFL): 35.06mm
6. ROHS COMPLIANT
7. PROTECTIVE BEVEL AS NEEDED
8. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
9. DESIGN WAVELENGTH: 587.6nm



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
RADIUS	80.56	22.91
SURFACE QUALITY	10-5	10-5
CLEAR APERTURE	Ø 22.5	Ø 22.5
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

LENS DCX BF 25 X 40 UNCTD TS

DWG NO

22569

SHEET  
5 OF 8