




NOTES:

1. SUBSTRATE:  
Calcium Fluoride, IR Grade (CaF<sub>2</sub>)
2. CENTERING TOLERANCE: <3 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1&S2: NONE
4.  FINE GRIND SURFACE
5. FOCAL LENGTH TOLERANCE: ±2%
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 5µm	50.8		
SHAPE	CONVEX	CONVEX	BFL @ 5µm	46.08	 <b>Edmund Optics®</b>	
RADIUS	38.64	38.64				
IRREGULARITY AT 632.8nm	λ	λ	TITLE	38.1mm Dia. x 50.8mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF <sub>2</sub> ) DCX Lens		
SURFACE QUALITY	60-40	60-40	DWG NO	24767		SHEET 10 OF 20
CLEAR APERTURE	ø34.29	ø34.29	ALL DIMS IN	mm		
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				