





FOCAL LENGTH (EFL): 36 ±0,36
BACK FOCAL LENGTH (BFL): 32,92

- 1 NIR I
R(AVG) ≤ 0,5% FROM 600 - 1050nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 16,505 CX Øe 17 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 17 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 18mm Dia x 36mm FL, NIR I Coated, Plano-Convex Lens DWG NO 26071 SHEET T SIZE A4 SHEET 1 OF 1	