





- NOTES:
- 1. SUBSTRATE:
Calcium Fluoride, IR Grade (CaF2)
 - 2. CENTERING TOLERANCE: <3 ARCMIN
 - 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2: NONE
 - 4.  FINE GRIND SURFACE
 - 5. FOCAL LENGTH TOLERANCE: ±2%
 - 6. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 5µm	200	 Edmund Optics®		
SHAPE	CONVEX	CONVEX	BFL @ 5µm	197.35			
RADIUS	158.49	158.49			TITLE	50.8mm Dia. x 200mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF2) DCX Lens	
IRREGULARITY AT 632.8nm	λ	λ					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN		DWG NO	24773	
CLEAR APERTURE	ø45.72	ø45.72					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	mm				SHEET 16 OF 20