




FOCAL LENGTH (EFL): 36 ±0,36
BACK FOCAL LENGTH (BFL): 34,63

- 1 VIS-EXT
R(AVG) ≤ 0,5% FROM 350 - 700nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 16,505 CX Øe 8,1 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 8,1 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION 	Edmund Optics® TITLE 9mm Dia x 36mm FL, VIS-EXT Coated, Plano-Convex Lens DWG NO 26320	
ALL DIMS IN: mm			SHEET SIZE A4 SHEET 1 OF 1	