


- NOTES:
- 1. SUBSTRATE: SODIUM SILICATE GLASS DOPED WITH SILVER NANOPARTICLES
  - 2. COATING: Uncoated
  - 3. TYPICAL ENERGY DENSITY LIMIT: 10 W/cm2
  - 4. EXTINCTION RATIO: >10,000:1
  - 5. WAVELENGTH RANGE: 1260-1360
  - 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div><div>THIRD ANGLE PROJECTION</div></div><div>ALL DIMS INmm</div><div><div>Edmund Optics®</div><div>Ultra-Thin Polarizer, 1310nm, 25mm Dia, Unc.</div></div></div>			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	40 - 20	40 - 20				
TRANSMISSION (%)	>87	>87				
ACCEPTANCE ANGLE	±20°	±20°				
BEVEL MAX FACE	PROTECTED AS NEEDED	PROTECTED AS NEEDED				
			TITLE	DWG NO	SHEET	
			26643	4 OF 12		