





FOCAL LENGTH (EFL):  $36 \pm 0,36$   
 BACK FOCAL LENGTH (BFL):  $34,63$

- 1 405nm V-COAT  
 R(ABS) < 0,25% @ 405nm @ 0° AOI

| LEFT SURFACE                                                                             |  |  | MATERIAL                                                                            |  | RIGHT SURFACE                                                                                      |  |        |                |       |  |                    |  |                 |  |
|------------------------------------------------------------------------------------------|--|--|-------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------|--|--------|----------------|-------|--|--------------------|--|-----------------|--|
| R 16,505 CX                                                                              |  |  | GLASS Fused Silica 458/678<br>Nd: 1,458                                             |  | R ∞ PL                                                                                             |  |        |                |       |  |                    |  |                 |  |
| Øe 5,4                                                                                   |  |  |                                                                                     |  | Øe 5,4                                                                                             |  |        |                |       |  |                    |  |                 |  |
| SEE NOTE 1                                                                               |  |  |                                                                                     |  | SEE NOTE 1                                                                                         |  |        |                |       |  |                    |  |                 |  |
| 3/ 3 (0,5) λ=632,8 nm                                                                    |  |  |                                                                                     |  | 3/ 3 (0,5) λ=632,8 nm                                                                              |  |        |                |       |  |                    |  |                 |  |
| 4/ -                                                                                     |  |  |                                                                                     |  | 4/ 2,18'                                                                                           |  |        |                |       |  |                    |  |                 |  |
| 5/ 40 - 20                                                                               |  |  |                                                                                     |  | 5/ 40 - 20                                                                                         |  |        |                |       |  |                    |  |                 |  |
| 6/ -                                                                                     |  |  | 6/ -                                                                                |  |                                                                                                    |  |        |                |       |  |                    |  |                 |  |
| PROTECTIVE CHAMFERS AS NEEDED                                                            |  |  | FIRST ANGLE<br>PROJECTION                                                           |  |  Edmund Optics® |  |        |                |       |  |                    |  |                 |  |
| ROHS:<br>COMPLIANT                                                                       |  |  |                                                                                     |  |                                                                                                    |  |        | SCALE:<br>NONE |       |  | λ = 587,6nm        |  |                 |  |
| SPECIFICATIONS SUBJECT TO CHANGE<br>WITHOUT NOTICE. DIMENSIONS ARE FOR<br>REFERENCE ONLY |  |  |  |  | TITLE<br><br>6mm Dia x 36mm FL, 405NM V-COAT<br>Coated, Plano-Convex Lens                          |  |        |                |       |  |                    |  |                 |  |
| FOR INFORMATION ONLY: DO NOT<br>MANUFACTURE PARTS TO THIS DRAWING                        |  |  |                                                                                     |  |                                                                                                    |  |        |                |       |  |                    |  |                 |  |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                                 |  |  | ALL<br>DIMS IN:                                                                     |  | mm                                                                                                 |  | DWG NO |                | 25858 |  | SHEET<br>T SIZE A4 |  | SHEET<br>1 OF 1 |  |