





FOCAL LENGTH (EFL): 21 ±0,21
BACK FOCAL LENGTH (BFL): 19,63

- 1 405nm V-COAT
R(ABS) < 0,25% @ 405nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE				
R 9,63 CX			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL				
Øe 5,4				Øe 5,4				
λ SEE NOTE 1				λ SEE NOTE 1				
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm				
4/ -				4/ 2,18'				
5/ 40 - 20				5/ 40 - 20				
6/ -			6/ -					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	6mm Dia x 21mm FL, 405NM V-COAT Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	25856	SHEET T SIZE A4	SHEET 1 OF 1