




FOCAL LENGTH (EFL): 27 ±0,27
BACK FOCAL LENGTH (BFL): 25,63

- 1 1064nm V-COAT
R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 12,38 CX Øe 8,1 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 8,1 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING FIRST ANGLE PROJECTION ALL DIMS IN: mm ED Edmund Optics® TITLE 9mm Dia x 27mm FL, 1064NM V-COAT Coated, Plano-Convex Lens DWG NO 25885 SHEET SIZE A4 SHEET 1 OF 1		