



NOTES:


1. SUBSTRATE: WIRE GRID ON DISPLAY GRADE GLASS
2. EXTINCTION RATIO:
1100:1 @ 900nm
3000:1 @ 1400nm
5500:1 @ 1900nm
5900:1 @ 2400nm
3. TRANSMISSION (%):
>81.5 @ 900nm
>87.7 @ 1400nm
>88.9 @ 1900nm
>88.6 @ 2400nm
4. WAVELENGTH RANGE: 700 - 2500nm
5. ORIENTATION OF AXIS: $0^\circ \pm 20^\circ$
NOTCHES ON POLARIZING FILM DEPICT DIRECTION OF POLARIZATION
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	NIR Wire Grid Polarizer, HC, 700nm-2500nm, 12.5mm Dia.	
ALL DIMS IN	mm	DWG NO	26993	SHEET 1 OF 6