



NOTES:


1. SUBSTRATE: WIRE GRID ON DISPLAY GRADE GLASS
2. EXTINCTION RATIO:
150:1 @ 900nm
500:1 @ 1400nm
800:1 @ 1900nm
1000:1 @ 2400nm
3. TRANSMISSION (%):
>88.1 @ 900nm
>91.0 @ 1400nm
>91.3 @ 1900nm
>90.3 @ 2400nm
4. WAVELENGTH RANGE: 700 - 2500nm
5. ORIENTATION OF AXIS: $0^\circ \pm 20^\circ$
NOTCHES ON POLARIZING FILM DEPICT DIRECTION OF POLARIZATION
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	NIR Wire Grid Polarizer, HT, 700nm-2500nm, 12.5mm Dia.	
ALL DIMS IN	mm	DWG NO	26998	SHEET 4 OF 6