





FOCAL LENGTH (EFL): 50,808 ± 0,51
 BACK FOCAL LENGTH (BFL): 44,084

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 39,87 CX Øe 49,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 49,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ 1,27' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 TITLE 50,8mm Dia x 50,81mm FL, Uncoated, Plano-Convex Lens DWG NO 29094 SHEET SIZE A4 SHEET 1 OF 1	