




NOTES:


1. LASER CLASS: IIIb
2. BEAM DIAMETER: 4.5 (typical)
BEAM DIVERGENCE: <0.5mrad, adjustable
3. MODULATION FREQUENCY: 0.1 - 50 kHz
4. OPERATING TEMPERATURE: +10 to +46°C
OPERATING VOLTAGE: 5V (USB POWERED)
5. OUTPUT POWER: 10mW
6. WAVELENGTH: 637 ±5nm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	Laser USB 637nm 10mW	
ALL DIMS IN	mm	DWG NO	26941	SHEET 1 OF 1