




NOTES:

1. LASER CLASS: IIIb
2. BEAM DIAMETER: 4.5 (typical)
BEAM DIVERGENCE: <0.5mrad, adjustable
3. MODULATION FREQUENCY: 0.1 - 50 kHz
4. OPERATING TEMPERATURE: +10 to +53°C
OPERATING VOLTAGE: 5V (USB POWERED)
5. OUTPUT POWER: 20mW
6. WAVELENGTH: 685 ±10nm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	Laser USB 685nm 20mW	
ALL DIMS IN	mm	DWG NO	26948	SHEET 1 OF 1