





f' : $10 \pm 0,1$

BACK FOCAL LENGTH (BFL): 7,6



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,17 CX Øe 7,2 λ AR Rave(425nm - 675nm, 0°) ≤ 0,40% 3/ 3 (0,5) λ=632,8 nm 4/ 5,8' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 7,2 λ AR Rave(425nm - 675nm, 0°) ≤ 0,40% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				Edmund Optics® 8mm Dia x 10mm FL, VIS 0 Coated, Plano-Convex Lens		
FIRST ANGLE PROJECTION 			TITLE			
ALL DIMS IN: mm			DWG NO			
			SHEET SIZE A4			
			SHEET 1 OF 1			