




f': 12 ± 0,12

BACK FOCAL LENGTH (BFL): 10



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 6,2 CX Øe 7,2 λ AR Rave(600nm - 1050nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - P			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 7,2 λ AR Rave(600nm - 1050nm, 0°) ≤ 0,50% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P		
PROTECTIVE CHAMFERS AS NEEDED				FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm		 Edmund Optics®		
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				TITLE		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	8mm Dia x 12mm FL, NIR I Coated, Plano-Convex Lens		
			DWG NO	71330	SHEET SIZE A4	SHEET 1 OF 1