




f' : $10 \pm 0,1$

BACK FOCAL LENGTH (BFL): 7,6



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,17 CX Øe 7,2 ⌘ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ 5,8' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 7,2 ⌘ AR R(880nm, 0°) ≤ 0,25% Rave(400nm - 870nm, 0°) ≤ 1,25% Rave(890nm - 1000nm, 0°) ≤ 1,25% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED				 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 8mm Dia x 10mm FL, VIS-NIR Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO 71326	SHEET SIZE A4	SHEET 1 OF 1