





f' : $76,2 \pm 0,76$

BACK FOCAL LENGTH (BFL): 68,948



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 39,38 CX Øe 49,3 ⌙ AR Rave(425nm - 675nm, 0°) ≤ 0,40% 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ - 			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 49,3 ⌙ AR Rave(425nm - 675nm, 0°) ≤ 0,40% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - 		
PROTECTIVE CHAMFERS AS NEEDED						
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	TITLE 50,8mm Dia x 76,1997mm FL, VIS 0 Coated, Plano-Convex Lens	
			DWG NO	71343		SHEET SIZE A4
					SHEET 1 OF 1	