


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

400nm Hard Coated Bandpass Interference Filter: 10nm FWHM
OD >4.0 Coating Performance
FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


400nm Hard Coated Bandpass Interference Filter OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


450nm Hard Coated Bandpass Interference Filter: 10nm FWHM
OD >4.0 Coating Performance
FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

450nm Hard Coated Bandpass Interference Filter OD >4.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


500nm Hard Coated Bandpass Interference Filter: 10nm FWHM OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


500nm Hard Coated Bandpass Interference Filter OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Hard Coated Bandpass Interference Filter: 10nm FWHM
OD >4.0 Coating Performance
FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Hard Coated Bandpass Interference Filter OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


600nm Hard Coated Bandpass Interference Filter: 10nm FWHM
OD >4.0 Coating Performance
FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


600nm Hard Coated Bandpass Interference Filter OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

650nm Hard Coated Bandpass Interference Filter: 10nm FWHM
OD >4.0 Coating Performance
FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

650nm Hard Coated Bandpass Interference Filter OD >4.0 Coating Performance FOR REFERENCE ONLY

