





+ 0.4861
x 0.5876
■ 0.6563



SURFACE: INA

IPA: 0.000 MM

SPOT DIAGRAM

CHROMATIC FOCAL SHIFT


49279INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 7.951
GD RADIUS : 18.565
SCALE BAR : 40

REFERENCE : CHIEF RAY


EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49279INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 744.0872 μm
DIFFRACTION LIMITED RANGE: 91.841 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT



POLYCHROMATIC DIFFRACTION MTF

49279INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49279INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)