



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES





CHROMATIC FOCAL SHIFT

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

493051NK
TUE DEC 16 2008
FIELD :
RMS RADIUS : 5.916
GD RADIUS : 16.401
SCALE BAR : 40

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

493051NK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 114.3661 μm
DIFFRACTION LIMITED RANGE: 13.192 μm
PUPIL ZONE: 0.0000



POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

493051NK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm
SURFACE: IMAGE

EO Edmund
optics | worldwide

www.edmundoptics.com