





49314INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 19.916
GD RADIUS : 53.812
SCALE BAR : 200


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49314INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 156.1192 μm
DIFFRACTION LIMITED RANGE: 9.477 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT



TRANSVERSE RAY FAN PLOT

49314INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49314INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

