





63706
MON APR 27 2009 UNITS ARE μm .
FIELD : 1
RMS RADIUS : 8.743
CED RADIUS : 25.709
SCALE BAR : 100

REFERENCE : CHIEF RAY


EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

63706
MON APR 27 2009
MAXIMUM FOCAL SHIFT RANGE: 70.1227 μm
DIFFRACTION LIMITED RANGE: 11.603 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



CHROMATIC FOCAL SHIFT




TRANSVERSE RAY FAN PLOT

63706
MON APR 27 2009
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

63706
MON APR 27 2009
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE



POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)