




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**




LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $\tau_p(\%)$	90
PASSBAND LIMIT $\lambda_p1$ (nm)	1300
CUT-OFF POSITION $\lambda_c$ (nm)	1000±6
STOPBAND LIMIT $\lambda_s$ (nm)	730
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	50.8 x 50.8mm, SCHOTT RG-1000 LONGPASS FILTER	
ALL DIMS IN	mm	DWG NO	32770	SHEET 1 OF 1