




NOTES:

1. SUBSTRATE:
Schott KG-5
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: NONE
3. FINE GRIND SURFACE
4. WAVELENGTH RANGE: 300 - 2700 nm
5. DENSITY (g/cm³): 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92
6. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

	S1	S2	THIRD ANGLE PROJECTION		TITLE	50 x 50mm SCHOTT KG-5 Heat Absorbing Glass	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN mm		DWG NO	49096	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					
							SHEET 1 OF 1