





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | VALUE |
|----------------------------|--------------------------------|
| CENTER WAVELENGTH (CWL) | 730 |
| FULL WIDTH HALF MAX (FWHM) | 10 |
| MINIMUM TRANSMISSION | ≥50% |
| BLOCKING WAVELENGTH | 200 - 1200 |
| SURFACE QUALITY | 80-50 |
| CONSTRUCTION | MOUNTED IN BLACK ANODIZED RING |
| COATING TYPE | TRADITIONAL COATED |

EO® Edmund Optics®



ALL DIMS IN

mm

TITLE

Ø12.7mm, 730 x 10 MOUNTED BANDPASS FILTER

DWG NO

62118

SHEET
1 OF 1