




FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A                               | VALUE                |
|--------------------------------------|----------------------|
| SHAPE                                | PLANO                |
| SPECTRAL TRANSMITTANCE $t_p(\%)$     | 93                   |
| PASSBAND LIMIT 1 $\lambda_{p1}$ (nm) | 750                  |
| CUT-OFF POSITION $\lambda_c$ (nm)    | 720±9                |
| STOPBAND LIMIT $\lambda_s$ (nm)      | 648                  |
| WAVELENGTH                           | IR                   |
| BEVEL                                | PROTECTIVE AS NEEDED |



|        |  |                 |  |
|--------|--|-----------------|--|
| TITLE  | 50.8 x 50.8mm, HOYA R-72 LONGPASS FILTER |                 |  |
| DWG NO | 66068                                    | SHEET<br>1 OF 1 |  |

ALL DIMS IN

mm