





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $\tau_p(\%)$	92
PASSBAND LIMIT $\lambda_p$ (nm)	550
CUT-OFF POSITION $\lambda_c$ (nm)	475±6
STOPBAND LIMIT $\lambda_s$ (nm)	410
WAVELENGTH	VIS
BEVEL	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø50mm, SCHOTT GG-475 LONGPASS FILTER

DWG NO

66082

SHEET  
1 OF 1