





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $\tau_p(\%)$	90
PASSBAND LIMIT λ_p (nm)	1300
CUT-OFF POSITION λ_c (nm)	1000±6
STOPBAND LIMIT λ_s (nm)	730
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

TITLE

Ø50mm, SCHOTT RG-1000 LONGPASS FILTER

DWG NO

66108

SHEET
1 OF 1