

1. CONSTRUCTION: MOUNTED IN BLACK ANODIZED RING
2. COATING (APPLY ACROSS COATING APERTURE)

PERFORMANCE SPECIFICATIONS:

FWHM: 25.7




REFLECTION %: >99

TRANSMISSION %: >90

3. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

4. TRANSMITTED WAVEFRONT DISTORTION RMS@ $<1\lambda$

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	OD4, Ø50mm, 514.5nm, NOTCH FILTER	
SHAPE	PLANO	PLANO			TITLE		
SURFACE QUALITY	60-40	60-40			TITLE		
CLEAR APERTURE	Ø45.21	Ø45.21	ALL DIMS IN	mm	DWG NO	67127	SHEET 1 OF 1