




M4 x 0.7 x 7 DEEP FOR MOUNTING THE KINEMATIC ASSEMBLY (2X)




□ 23.50



18.60

M3 ADJUSTMENT LOCKING HEX SOCKET SET SCREWS (3)




□ 23.00

M3 x 0.2 HEX SOCKET ADJUSTMENT SCREWS (3X)

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics**®

THIRD ANGLE PROJECTION 		TITLE	SM FLAT KINEMATIC MOUNT 3-SCREW	
ALL DIMS IN	mm	DWG NO	34723	SHEET 1 OF 1