




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

	VALUE
OPTICAL DENSITY	≥ 4.0
CENTER WAVELENGTH (CWL)	$254 + 10.0/-0.0$ nm
FULL WIDTH HALF MAX (FWHM)	40 ± 8 nm
MINIMUM TRANSMISSION	$> 20\%$
BLOCKING	200 - 10000nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]



ALL DIMS IN

mm

TITLE

$\varnothing 25$ mm, 254nm x 40nm, MOUNTED
BANDPASS FILTER

DWG NO

67809

SHEET
1 OF 1