





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	514.5nm
FULL WIDTH HALF MAX (FWHM)	$3 \pm 1.0\text{nm}$
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	400 - 509 & 520 - 700nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE	Ø25mm, 514.5nm CWL, 3nm FWHM, HARD COATED LASER CLEAN-UP FILTER		
DWG NO	68874	SHEET 1 OF 1	