





Surface: IMA

Spot Diagram

63709INK
4/24/2017
Units are μm.
Field : 1
RMS radius : 1.121
GEO radius : 2.472
Scale bar : 10
Airy Radius: 3.182 μm. Legend items refer to Wavelengths
Reference : Chief Ray

Edmund Optics
HTTP://WWW.EDMUNDOPTICS.COM

63709INK.ZMX
Configuration 1 of 1



Chromatic Focal Shift

63709INK
4/24/2017
Maximum Focal Shift Range: 40.7452 μm
Diffraction Limited Range: 46.324 μm
Pupil Zone: 0.0000

Edmund Optics
HTTP://WWW.EDMUNDOPTICS.COM

63709INK.ZMX
Configuration 1 of 1

OBJ: 0.0000 (deg)



—Diff. Limit-Tangential —Diff. Limit-Sagittal —0.0000 (deg)-Tangential —0.0000 (deg)-Sagittal

Transverse Ray Fan Plot

63709INK
4/24/2017
Maximum Scale: ± 5.000 μm.
0.486 0.588 0.656
Surface: Image

Edmund Optics
HTTP://WWW.EDMUNDOPTICS.COM

63709INK.ZMX
Configuration 1 of 1

Polychromatic Diffraction MTF

63709INK
4/24/2017
Data for 0.4861 to 0.6563 μm.
Surface: Image
Legend items refer to Field positions

Edmund Optics
HTTP://WWW.EDMUNDOPTICS.COM

63709INK.ZMX
Configuration 1 of 1