NOTES:

- 1. SUBSTRATE: GRADE A FINE ANNEALED SCHOTT: N-BK7 517/642
- 2. ROHS COMPLIANT
- 3. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN 3 ARCMIN
- 4. COATING (APPLY ACROSS COATING APERTURE)
 SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION
 S1.

R(abs) = 30% ±5% @ 550nm R(abs) = 30% ±10% FROM 400-700nm T(abs) = 70% ±5% @ 550nm T(abs) = 70% ±10% FROM 400-700nm VISUAL COLOR = NEUTRAL


S2: BBAR


R(abs) ≤ 2.0% FROM 400-700nm R(avg) ≤ 1.0% FROM 400-700nm

5.

FINE GRIND SURFACE

MARK IDENTIFIES BEAMSPLITTER SURFACE





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE FLATNESS	2λ PER 25mm	2λ PER 25mm			
SURFACE QUALITY	60 - 40	60 - 40			
MIN CLEAR APERTURE	21.25 x 32.30	21.25 x 32.30			
MIN COATING APERTURE	21.25 x 32.30	21.25 x 32.30			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

		Edmund Optics ®		
THIRD ANG PROJECTIO		TITLE	BS VIS 30R/70T 25X38MM 1MM THK	
ALL DIMS IN	mm	DWG NO	35935	SHEET 1 OF 1