NOTES:

SUBSTRATE MATERIAL:
 FUSED SILICA

2. CENTERING BEAM DEVIATION:

\$1 & \$2 BEAM DEVIATION TO BE <3 ARCMIN \$4 & \$5 BEAM DEVIATION TO BE <3 ARCMIN


3. COATING (APPLY ACROSS CLEAR APERTURE)

\$1, \$2, \$3 & \$4: NONE \$5: EXTINCTION RATIO: Tp/Ts >1000:1 @ 532nm TRANSMISSION: TP >98% @ 532nm

DAMAGE THRESHOLD, PULSED: TYPICAL: 20 J/cm2 @ 1064nm 10ns, 20Hz

4. FINE GROUND SURFACE

5. ROHS COMPLIANT



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE				Edmund Option	CS®
SURFACE FLATNESS	λ/6				12.7mm x 532nm, HIGH ENERGY POLARIZING CUBE BEAMSPLITTER	
SURFACE QUALITY	20-10	THIRD ANGLE PROJECTION		TITLE		
MIN CLEAR APERTURE	11.43 x 11.43					
BEVEL MAX FACE	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	88233	SHEET 1 OF 1