


NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: ALUMINUM COATED W/ PROTECTIVE OVERCOAT
R(AVG)>85% FROM 400-700nm, @ 45° AOI



S2: NONE
3. FINE GRIND SURFACE

- 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	44.55 x 31.5	31.5 x 31.5				
COATING APERTURE	44.55 x 31.5	31.5 x 31.5	TITLE 35mm, Aluminum Coated, N-BK7 Right Angle Prism			
SURFACE FLATNESS	λ/4	λ/4				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO 32530	SHEET 1 OF 1