




- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: RABS ≤0.25% @ 880nm RAVG ≤1.25% @ 400 - 870nm RAVG ≤1.25% @ 890 - 1000nm
- FINE GRIND SURFACE /4.\
- 5. ROHS COMPLIANT







R INFORMATION ON F DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

4.5

- I

	12	50	1			Edmund Optic	S [®] ∣
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40				TITLE	10mm SQ., 2mm THICK, VIS-NIR COATED λ/4 N-BK7 WINDOW	
CLEAR APERTURE	9.00 x 9.00	9.00 x 9.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	49631	Sheet 1 Of 1